



# CorePro LEDbulbs

## CorePro LEDbulb ND 12.5-100W A60 E27 865

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost.

### Product data

General Information		Warm Up Time to 60% Light (Nom)	
Base	E27 [ E27]		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.5
Nominal Lifetime (Nom)	15000 h	Voltage (Nom)	220-240 V
Switching Cycle	50000X	<b>Temperature</b>	
Technical Type	12.5-100W	T-Case Maximum (Nom)	85 °C
<b>Light Technical</b>		<b>Controls and Dimming</b>	
Color Code	865 [ CCT of 6500K]	Dimmable	No
Beam Angle (Nom)	200 °	<b>Mechanical and Housing</b>	
Initial lumen (Nom)	1521 lm	Bulb Finish	Frosted
Color Designation	Cool Daylight	<b>Approval and Application</b>	
Correlated Color Temperature (Nom)	6500 K	Energy Efficiency Label (EEL)	A+
Luminous Efficacy (rated) (Nom)	121.00 lm/W	Energy Consumption kWh/1000 h	13 kWh
Color Consistency	<6	<b>Product Data</b>	
Color Rendering Index (Nom)	80	Order product name	CorePro LEDbulb ND 12.5-100W A60 E27 865
LLMF At End Of Nominal Lifetime (Nom)	70 %	EAN/UPC - Product	8718696577813
<b>Operating and Electrical</b>		Order code	344341
Input Frequency	50 to 60 Hz	Numerator - Quantity Per Pack	1
Power (Rated) (Nom)	12.5 W	Numerator - Packs per outer box	10
Lamp Current (Nom)	115 mA	Material Nr. (12NC)	929001312502
Wattage Equivalent	100 W		
Starting Time (Nom)	0.5 s		

# CorePro LEDbulbs

Net Weight (Piece) 0.076 kg



## Dimensional drawing



Product	D	C
CorePro LEDbulb ND 12.5-100W A60 E27 865	60 mm	110 mm


A60 220-240V 12.5W-100W 6500K E27 ND

## Photometric data



CorePro LEDbulb 100W E27 865 FR A60

CorePro LEDbulb 40W E27 865 FR A60




CorePro LEDbulb 100W E27 840 FR A60

# CorePro LEDbulbs

## Lifetime



LEDbulb 100W E27 840 FR A60



LEDbulb 100W E27 840 FR A60

