



# LED PAR38

## 12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	25,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	835 [CCT of 3500K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	900 lm
Luminous Intensity (Nom)	1,900 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	75.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	12 W
Lamp Current (Nom)	112 mA

Wattage Equivalent	90 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	75 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh


Product Data	
Order product name	12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1
Full product name	12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1
Order code	929001320104
Material Nr. (12NC)	929001320104

LED PAR38

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677474706
Numerator - Packs per outer box	6



EAN/UPC - Case	50046677474701
----------------	----------------

Dimensional drawing




Product	D	C
12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1	121 mm	132 mm

Photometric data



Accent Lighting Spots - 12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1


Light Distribution Diagram - 12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1




Spectral Power Distribution Colour - 12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1

LED PAR38

Lifetime



Life Expectancy Diagram - 12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1



Lumen Maintenance Diagram - 12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1

