



LED PAR30 S/L

10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	25,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	850 lm
Luminous Intensity (Nom)	3,300 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	86 mA


Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB

LED PAR30 S/L

Full product name	10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB
Order code	529784
Material Nr. (12NC)	929001320704
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	046677529789
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677529784

Dimensional drawing




Product	D	C
10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB	94 mm	93 mm


Photometric data



Accent Lighting Spots - 10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB



Light Distribution Diagram - 10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB




Spectral Power Distribution Colour - 10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB

LED PAR30 S/L

Lifetime



Life Expectancy Diagram - 10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB



Lumen Maintenance Diagram - 10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB

