

**PHILIPS**

Eco passport

## 10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB LED PAR30 S/L

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.



### Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



#### Energy

- **Dimmable:** Yes
- **Luminous Efficacy (rated) (Nom):** 85.00 lm/W
- **Power (Rated) (Nom):** 10 W



#### Circularity

- **Nominal Lifetime (Nom):** 25000 h



#### Packaging

- **SAP Weight Paper Unit (Case):** 0.521 kg
- **SAP Weight Paper Unit (Piece):** 0.054 kg



#### Substances

- **EU REACH restrictions compliant:** Yes
- **EU RoHS compliant:** Yes



#### Weight & Materials

- **Net Weight (Piece):** 0.285 kg

Further reading at:

<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2020 Signify Holding. All rights reserved.