



MASTER LEDspot PAR

MAS LEDspot D 13-100W E27 927 PAR38 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	25,000 hour(s)
Switching Cycle	25,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927
Beam Angle (Nom)	25 degree(s)
Luminous Flux	1,000 lm
Luminous Intensity (Nom)	4,000 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	76.92 lm/W
Color Consistency	<6
Color rendering index (CRI)	90


LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	13 W
Lamp Current (Nom)	65 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C

MASTER LEDspot PAR

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	13 kWh
Product Data	
Order product name	MAS LEDspot D 13-100W E27 927 PAR38 25D



Full product name	MAS LEDspot D 13-100W E27 927 PAR38 25D
Full product code	871869671410200
Order code	929001322508
Material Nr. (12NC)	929001322508
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696714102
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696714119

Dimensional drawing



Product	D	C
MAS LEDspot D 13-100W E27 927 PAR38 25D	122 mm	134 mm

Photometric data




Accent Lighting Spots - MAS LEDspot D 13-100W E27 927 PAR38 25D

Spectral Power Distribution Colour - MAS LEDspot D 13-100W E27 927 PAR38 25D


MASTER LEDspot PAR

Photometric data




Light Distribution Diagram - MAS LEDspot D 13-100W E27 927 PAR38 25D

Lifetime



Life Expectancy Diagram - MAS LEDspot D 13-100W E27 927 PAR38 25D



Lumen Maintenance Diagram - MAS LEDspot D 13-100W E27 927 PAR38 25D

