



MASTER LEDspot PAR

MAS LEDspot D 13-100W E27 927 PAR38 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data


General Information		LLMF at end of nominal lifetime (nom.)	
Cap base	E27 [E27]	70 %	
Nominal lifetime (nom.)	25000 h	Operating and Electrical	
Technical type	13-100W	Input frequency	50 to 60 Hz
Light Technical		Power (Rated) (Nom)	13 W
Colour Code	927	Lamp current (nom.)	65 mA
Beam Angle (Nom)	25 °	Wattage equivalent	100 W
Lamp Luminous Flux 25°C EL (Nom)	1000 lm	Starting time (nom.)	0.5 s
Lamp Luminous Flux (Nom)	1000 lm	Warm-up time to 60% light (nom.)	0.5 s
Luminous intensity (nom.)	4000 cd	Power factor (nom.)	0.9
Colour Designation	Warm white (WW)	Voltage (Nom)	220-240 V
Rated beam angle	25 °	Controls and Dimming	
Colour Temperature, horizontal (Nom)	2700 K	Dimmable	Yes
Lamp Luminous Efficacy EM (Nom)	76.92 lm/W	Approval and Application	
Colour consistency	<6	Energy efficiency label (EEL)	A+
Colour Rendering Index,horiz (Nom)	90		

MASTER LEDspot PAR

Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	13 kWh
Product Data	
Full product code	871869671410200
Order product name	MAS LEDspot D 13-100W E27 927 PAR38 25D
EAN/UPC – product	8718696714102

Order code	929001322508
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001322508
Net weight (piece)	0.385 kg


Dimensional drawing




PAR38 220-240V 13-100W 2700K E27 D

Product	D	C
MAS LEDspot D 13-100W E27 927 PAR38 25D	122 mm	134 mm

Photometric data




Product Information 11 Photo Lighting E 11 Page 17



MASTER LEDspot PAR 100W E27 827 25D


MASTER LEDspot PAR 100W E27 827 25D




MASTER LEDspot PAR 100W E27 827 25D

MASTER LEDspot PAR

Lifetime



MASTER LEDspot PAR 50W E27 827 25D



MASTER LEDspot PAR 50W E27 827 25D

