

PHILIPS

Eco passport

MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D MASTER LEDspot PAR

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.



Our Eco passport



Energy

- Dimmable: Yes
- Energy efficiency label (EEL): A+
- Luminous efficacy (rated) (nom.): 92.63 lm/W
- Power (Rated) (Nom): 9.5 W



Circularity

- Nominal lifetime (nom.): 25000 h



Packaging

- SAP Weight Paper Unit (Case): 0.448 kg
- SAP Weight Paper Unit (Piece): 0.045 kg



Substances

- EU RoHS compliant: No



Weight & Materials

- Net weight (piece): 0.230 kg

Energy efficiency ranking / External awards

