



Candle/Decorative LED

LED 25W T25 E14 WW FR ND SRT4

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Base	E14 [E14]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	3.2-25W
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	160 °
Initial lumen (Nom)	250 lm
Luminous Flux (Rated) (Nom)	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	78.13 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 Hz


Power (Rated) (Nom)	3.2 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	230 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Energy Efficiency Label (EEL)	A+

Candle/Decorative LED

Energy Consumption kWh/1000 h	4 kWh
Product Data	
Order product name	LED 25W T25 E14 WW FR ND SRT4
EAN/UPC - Product	8718696703137
Order code	346551

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001325801
Net Weight (Piece)	0.020 kg


Dimensional drawing




Capsule 230V 3-25W 250lm 2700K E14 ND

Product	D	C
LED 25W T25 E14 WW FR ND SRT4	25 mm	71 mm


Photometric data



CorePro LEDcapsule MV 35W G9 827 Capsule



LEDCandle 25W E14 T25 Frosted 827 16D ND




LEDCandle 25W E14 T25 Frosted 827 16D ND

Candle/Decorative LED

Lifetime



LEDCandle 25W E14 T25 Frosted 827 16D ND



LEDCandle 25W E14 T25 Frosted 827 16D ND

