



Candle LED

LED 25W T25 E14 WW FR ND SRT4

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

| General Information | |
|---------------------------------------|--------------------|
| Cap-Base | E14 [E14] |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 50,000 |
| Rated Lifetime (Hours) | 15,000 hour(s) |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 827 [CCT of 2700K] |
| Beam Angle (Nom) | 160 degree(s) |
| Luminous Flux | 250 lm |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Luminous Efficacy (rated) (Nom) | 78.13 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Line Frequency | 50 Hz |
| Input Frequency | 50 Hz |
| Power Consumption | 3.2 W |


| Lamp Current (Nom) | 35 mA |
|-------------------------------|-------------------------------|
| Wattage Equivalent | 25 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.4 |
| Voltage (Nom) | 230 V |
| Temperature | |
| T-Case Maximum (Nom) | 176 °F |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Shape | T25 [T 25mm] |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 4 kWh |
| EyeComfort | Yes |
| Product Data | |
| Order product name | LED 25W T25 E14 WW FR ND SRT4 |

Candle LED

| | |
|-------------------------------|-------------------------------|
| Full product name | LED 25W T25 E14 WW FR ND SRT4 |
| Full product code | 871869670313700 |
| Order code | 346551 |
| Material Nr. (12NC) | 929001325801 |
| Numerator - Quantity Per Pack | 1 |



| | |
|---------------------------------|---------------|
| EAN/UPC - Product/Case | 8718696703137 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8718696703144 |

Dimensional drawing




| Product | D | C |
|-------------------------------|--------|--------------|
| LED 25W T25 E14 WW FR ND SRT4 | 1 inch | 2-13/16 inch |

Photometric data



Spectral Power Distribution Colour - LED 25W T25 E14 WW FR ND SRT4



General uniform lighting - LED 25W T25 E14 WW FR ND SRT4



Light Distribution Diagram - LED 25W T25 E14 WW FR ND SRT4

Candle LED

Lifetime



Life Expectancy Diagram - LED 25W T25 E14 WW FR ND SRT4

Lumen Maintenance Diagram - LED 25W T25 E14 WW FR ND SRT4

