

PHILIPS

Eco passport

Classic LEDCandle D 5-40W B35 E14 827 CL

Classic filament LED candles and lusters

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.



Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

Energy

- **Dimmable:** Yes
- **Energy Efficiency Label (EEL):** A+
- **Luminous Efficacy (rated) (Nom):** 94.00 lm/W
- **Power (Rated) (Nom):** 5 W

Circularity

- **Nominal Lifetime (Nom):** 15000 h

Packaging

- **SAP Weight Paper Unit (Case):** 0.242 kg
- **SAP Weight Paper Unit (Piece):** 0.013 kg

Substances

- **BFR policy compliant:** Yes
- **EU REACH restrictions compliant:** Yes
- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** Yes
- **PVC policy compliant:** Yes

Weight & Materials

- **Net Weight (Piece):** 0.014 kg

Energy efficiency ranking / External awards



Further reading at:
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2020 Signify Holding. All rights reserved.