

PHILIPS

Eco passport

Classic LEDLuster D 2.7-25W P45 E14 827 CL

Classic filament LED candles and lustres



Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.

Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- **Dimmable:** Yes
- **Energy efficiency label (EEL):** A++
- **Luminous efficacy (rated) (nom.):** 92.59 lm/W
- **Power (Rated) (Nom):** 2.7 W



Circularity

- **Nominal lifetime (nom.):** 15000 h



Packaging

- **SAP Weight Paper Unit (Case):** 0.304 kg
- **SAP Weight Paper Unit (Piece):** 0.016 kg



Weight & Materials

- **Net weight (piece):** 0.014 kg

Energy efficiency ranking / External awards



Further reading at:
<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2020 Signify Holding. All rights reserved.