



# Classic filament LED candles and lustres

## CLA LEDLuster D 2.7-25W P45 E14 827 CL

Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.

### Product data

General Information		Lamp current (nom.)	
Cap base	E14 [ E14]		12 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	25 W
Switching cycle	20000X	Starting time (nom.)	0.5 s
Technical type	2.7-25W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour code	827 [ CCT of 2,700 K]	T-Case maximum (nom.)	40 °C
Luminous flux (nom.)	250 lm		
Luminous flux (rated) (nom.)	250 lm	Controls and Dimming	
Colour designation	Warm white (WW)	Dimmable	Yes
Correlated colour temperature (nom.)	2700 K	Mechanical and Housing	
Luminous efficacy (rated) (nom.)	92.59 lm/W	Bulb finish	Clear (CL)
Colour consistency	<6	Approval and Application	
Color rendering index (nom.)	80	Energy efficiency label (EEL)	A++
LLMF at end of nominal lifetime (nom.)	70 %	Energy Consumption kWh/1000 h	3 kWh
Operating and Electrical			
Input frequency	50 to 60 Hz		
Power (Rated) (Nom)	2.7 W		


# Classic filament LED candles and lustres

## Product Data

Full product code	871869670986300
Order product name	CLA LEDLuster D 2.7-25W P45 E14 827 CL
EAN/UPC – product	8718696709863
Order code	70986300
Numerator – quantity per pack	1

Numerator – packs per outer box	10
Material no. (12NC)	929001332302
Net weight (piece)	0.014 kg



## Dimensional drawing




Candle P45 230V 3-25W250lm 2700K D Clear

Product	D	C
CLA LEDLuster D 2.7-25W P45 E14 827 CL	45 mm	85 mm

## Photometric data




LEDbulb 25W E14 827 CL P45




LEDbulb 25W E14 827 CL B35

## Classic filament LED candles and lustres

### Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

