


PHILIPS

Eco passport

CLA LEDLuster D 2.7-25W P45 E27 827 CL

Classic filament LED candles and lustres

Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.



Our Eco passport



Energy

- Dimmable: Yes
- Energy efficiency label (EEL): A++
- Luminous efficacy (rated) (nom.): 92.59 lm/W
- Power (Rated) (Nom): 2.7 W



Circularity

- Nominal lifetime (nom.): 15000 h



Packaging

- SAP Weight Paper Unit (Case): 0.304 kg
- SAP Weight Paper Unit (Piece): 0.016 kg



Substances

- EU RoHS compliant: No



Weight & Materials

- Net weight (piece): 0.014 kg

Energy efficiency ranking / External awards

