



Classic filament LED candles and lustres

CLA LEDLuster D 2.7-25W P45 E27 827 CL

Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	2.7-25W
Light Technical	
Colour code	827 [CCT of 2,700 K]
Luminous flux (nom.)	250 lm
Luminous flux (rated) (nom.)	250 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	92.59 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	2.7 W

Lamp current (nom.)	12 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	40 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy efficiency label (EEL)	A++
Energy Consumption kWh/1000 h	3 kWh


Classic filament LED candles and lustres

Product Data

Full product code	871869670988700
Order product name	CLA LEDLuster D 2.7-25W P45 E27 827 CL
EAN/UPC – product	8718696709887
Order code	70988700
Numerator – quantity per pack	1

Numerator – packs per outer box	10
Material no. (12NC)	929001332402
Net weight (piece)	0.014 kg



Dimensional drawing




Candle P45 230V 3-25W250lm 2700K D Clear

Product	D	C
CLA LEDLuster D 2.7-25W P45 E27 827 CL	45 mm	80 mm

Photometric data




LEDbulb 25W E27 827 CL P45




LEDbulb 25W E14 827 CL B35

Classic filament LED candles and lustres

Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

