

Decorative LED bulbs

CLA LEDBulb D 7.5-48W A60 B22 820 GOLD

The new Deco collection transforms your home with a perfect blend of warm white light and a lean, minimalistic lighting experience. With long lifetime, up to 90% energy savings, no flickering and an instant full-level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

Product data

General Information	
Cap base	B22 [B22]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	7.5-48W
Light Technical	
Colour code	820 [CCT of 2,000 K]
Luminous flux (nom.)	610 lm
Luminous flux (rated) (nom.)	610 lm
Colour designation	Flame
Correlated colour temperature (nom.)	2000 K
Luminous efficacy (rated) (nom.)	81.33 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	7.5 W
Lamp current (nom.)	36 mA
Wattage equivalent	48 W


Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	55 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Amber
Approval and Application	
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871869670958000
Order product name	CLA LEDBulb D 7.5-48W A60 B22 820 GOLD
EAN/UPC – product	8718696709580

Decorative LED bulbs

Order code	70958000
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001333002

Net weight (piece)	0.030 kg
--------------------	----------


Dimensional drawing




Bulb A60 230V 7.5-48W600lm 2000K D Amber

Product	D	C
CLA LEDBulb D 7.5-48W A60 B22 820 GOLD	60 mm	102 mm


Photometric data



LEDbulb 48W B22 820 GOLD A60



LEDbulb 48W E27 820 GOLD A60




LEDbulb 40W E27 827 CL A60 D

Decorative LED bulbs

Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

