



MASTER Value Decorative LED bulbs

LED classic CM 48W A60 E27 WW CL D SRT4

The new collection of MASTER Value Decorative LED bulbs will transform any home. decorative LED bulbs are ideal for decorative lighting projects, they offer a perfect blend of (warm) white light and a minimalistic lighting experience. With a very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you can enjoy soft and evenly distributed light. And thanks to the dimmable LED bulbs, you can dial it up or down to suit your mood. So, you can create a welcoming harmony in your space with decorative LED lamps that shine with trendy and stylish charm.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	610 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	81.33 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	7.5 W
Lamp Current (Nom)	36 mA
Wattage Equivalent	48 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C


Datasheet, 2023, May 15 data subject to change

MASTER Value Decorative LED bulbs

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Consumption kWh/1000 h	8 kWh
EyeComfort	Yes
Product Data	
Order product name	LED classic CM 48W A60 E27 WW CL D SRT4


Full product name	LED classic CM 48W A60 E27 WW CL D SRT4	
Full product code	871869670926900	
Order code	929001333501	
Material Nr. (12NC)	929001333501	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8718696709269	
Numerator - Packs per outer box	4	
EAN/UPC - Case	8718696709276	

Dimensional drawing




Product	D	С
LED classic CM 48W A60 E27 WW CL D SRT4	60 mm	104 mm

Photometric data




General uniform lighting - LED classic CM 48W A60 E27 WW CL D SRT4



Light Distribution Diagram - LED classic CM 48W A60 E27 WW CL D SRT4


MASTER Value Decorative LED bulbs


Photometric data



Spectral Power Distribution Colour - LED classic CM 48W A60 E27 WW CL D SRT4

Lifetime





Life Expectancy Diagram - LED classic CM 48W A60 E27 WW CL D SRT4 $\,$

Lumen Maintenance Diagram - LED classic CM 48W A60 E27 WW CL D SRT4



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.