

Master LEDtube Universal 1200mm UO 16W865 T8 MASTER LEDtube Universal T8

The new Philips MASTER LEDtube Universal T8 brings ease and simplicity to your lighting project. That's because you do not need to match the driver technology anymore: a unique design enables the Philips MASTER LEDtube Universal T8 to directly fit in luminaires operating on either electromagnetic ballasts or HF electronic ballasts or mains power connection. It is so simple to operate and you no longer need to stock two types of tubes! Perfectly safe, reliable & easy to install Philips MASTER LEDtube Universal T8 is the ideal alternative to standard fluorescent tubes to maximize value over lifetime with high energy saving and lower maintenance costs.



Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

Energy

- **Dimmable:** No
- **Energy Efficiency Label:** A++
- **Power (Rated) (Nom):** 16 W

Circularity

- **Nominal Lifetime (Nom):** 60000 h

Packaging

- **SAP Weight Paper Unit (Case):** 0.910 kg
- **SAP Weight Paper Unit (Piece):** 0.030 kg

Substances

- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** No
- **Halogen free compliant:** No

Weight & Materials

- **Net Weight (Piece):** 0.270 kg