

## Master LEDtube Universal 1200mm UO 16W865 T8 MASTER LEDtube Universal T8

The new Philips MASTER LEDtube Universal T8 brings ease and simplicity to your lighting project. You don't need to match the driver technology any more: a unique design enables the Philips MASTER LEDtube Universal T8 to directly fit in luminaires operating on either electromagnetic ballasts or HF electronic ballasts or mains power connection. It is so simple to operate and you no longer need to stock two types of tubes! Perfectly safe, reliable and easy to install, the Philips MASTER LEDtube Universal T8 is the ideal alternative to standard fluorescent tubes: to maximise value over lifetime with high energy savings and lower maintenance costs.



### Our Eco passport



#### Energy

- Dimmable: No
- Energy efficiency label (EEL): A++
- Power (Rated) (Nom): 16 W



#### Circularity

- Nominal lifetime (nom.): 60000 h



#### Packaging

- SAP Weight Paper Unit (Case): 0.910 kg
- SAP Weight Paper Unit (Piece): 0.030 kg



#### Substances

- EU RoHS compliant: No



#### Weight & Materials

- Net weight (piece): 0.270 kg

#### Energy efficiency ranking / External awards

