



MASTER LEDtube Universal T8

Master LEDtube Universal 1500mm UO 24W840 T8

The new Philips MASTER LEDtube Universal T8 brings ease and simplicity to your lighting project. That's because you do not need to match the driver technology anymore: a unique design enables the Philips MASTER LEDtube Universal T8 to directly fit in luminaires operating on either electromagnetic ballasts or HF electronic ballasts or mains power connection. It is so simple to operate and you no longer need to stock two types of tubes! Perfectly safe, reliable & easy to install Philips MASTER LEDtube Universal T8 is the ideal alternative to standard fluorescent tubes to maximize value over lifetime with high energy saving and lower maintenance costs.

Product data


General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Input Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power (Rated) (Nom)	24 W
Nominal Lifetime (Nom)	60000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time to 60% Light (Nom)	0.5 s
Light Technical		Power Factor (Nom)	0.9
Colour Code	840 [CCT of 4000K]	Voltage (Nom)	220-240 V
Luminous Flux (Nom)	3700 lm	Temperature	
Colour Temperature, horizontal (Nom)	4000 K	T-Ambient (Max)	45 °C
Color Consistency	<6	T-Ambient (Min)	-20 °C
Colour Rendering Index horiz (Nom)	83	T-Storage (Max)	65 °C
LLMF At End Of Nominal Lifetime (Nom)	70 %	T-Storage (Min)	-40 °C

MASTER LEDtube Universal T8

T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Plastic
Product Length	1500 mm
Approval and Application	
Energy Efficiency Label	A++
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking KEMA Keur certificate

Energy Consumption kWh/1000 h	24 kWh
Product Data	
Full product code	871869670533900
Order product name	Master LEDtube Universal 1500mm UO 24W840 T8
EAN/UPC - Product	8718696705339
Order code	70533900
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001336402
Net Weight (Piece)	0.450 kg


Dimensional drawing



TLED 24.5W-58W 3700lm 160D 4000K ND


Product	D1	D2	A1	A2	A3
Master LEDtube Universal 1500mm UO 24W840 T8	25.7 mm	28 mm	1500 mm	1507.1 mm	1514.2 mm

Photometric data



General Uniform Lighting
1 x 1500 mm 24W 840 3700lm
Page 11

LEDtube 1500mm 24W G13 840 3700lm



LEDtube 1500mm 24W G13 840 3700lm


MASTER LEDtube Universal T8

Photometric data



LEDtube 1200mm 16W G13

Lifetime



LEDtube 1200mm 16W G13



LEDtube 1200mm 16W G13

