

Ecofit Ledtubes T8



Ecofit LEDtube 1500mm 20W 840 T8 I

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information		Power Consumption	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		20 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.5
Flux measurement reference	Sphere	Voltage (Nom)	220-240 V
EU RoHS compliant	Yes	Temperature	
Light Technical		Ambient temperature range	-20 °C to 45 °C
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	60 °C
Beam Angle (Nom)	240 degree(s)	Controls and Dimming	
Luminous Flux	2,000 lm	Dimmable	No
Color Designation	Cool White (CW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	4000 K	Bulb Material	Glass
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Product Length	1,500 mm
Color Consistency	<6	Bulb Shape	T8
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Efficiency Class	F
Operating and Electrical		Energy Saving Product	Yes
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Ecofit Ledtubes T8


Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	20 kWh
EPREL Registration Number	491860
Product Data	
Order product name	Ecofit LEDtube 1500mm 20W 840 T8 I
Full product name	Ecofit LEDtube 1500mm 20W 840 T8 I
Full product code	871869969708200

Order code	929001338122
Material Nr. (12NC)	929001338122
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699697082
Numerator - Packs per outer box	20
EAN/UPC - Case	8718699697099


Dimensional drawing

Product	D1	D2	A1	A2	A3
Ecofit LEDtube 1500mm 20W 840 T8 I	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm


Photometric data



Light Distribution Diagram - Ecofit LEDtube 1500mm 20W 840 T8 I




Spectral Power Distribution Colour - Ecofit LEDtube 1500mm 20W 840 T8 I




Ecofit Ledtubes T8


Lifetime




Lumen Maintenance Diagram - Ecofit LEDtube 1500mm 20W 840 T8 I




Lumen Maintenance Diagram - Ecofit LEDtube 1500mm 20W 840 T8 I



Life Expectancy Diagram - Ecofit LEDtube 1500mm 20W 840 T8 I



Life Expectancy Diagram - Ecofit LEDtube 1500mm 20W 840 T8 I



Life Expectancy Diagram - Ecofit LEDtube 1500mm 20W 840 T8 I

Ecofit Ledtubes T8

