



Ecofit Ledtubes T8

Ecofit LEDtube 1500mm 20W 865 T8

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data


General Information		Warm-up time to 60% light (nom.)	
Cap base	G13 [Medium Bi-Pin Fluorescent]		0.5 s
Main application	Industrial	Power factor (nom.)	0.5
Nominal lifetime (nom.)	15000 h	Voltage (Nom)	220-240 V
Switching cycle	50000X	Temperature	
Light Technical		T ambient (max.)	45 °C
Colour Code	865 [CCT of 6,500 K]	T ambient (min.)	-20 °C
Technical Beam Angle (Nom)	240 °	T storage (max.)	65 °C
Lamp Luminous Flux 25°C EL (Nom)	2000 lm	T storage (min.)	-40 °C
Lamp Luminous Flux (Nom)	2000 lm	T-Case maximum (nom.)	60 °C
Colour Temperature, horizontal (Nom)	6500 K	Controls and Dimming	
Lamp Luminous Efficacy EM (Nom)	100.00 lm/W	Dimmable	No
Colour consistency	<6	Mechanical and Housing	
Colour Rendering Index, horiz (Nom)	80	Product length	1500 mm
LLMF at end of nominal lifetime (nom.)	70 %	Approval and Application	
Operating and Electrical		Energy efficiency label (EEL)	A+
Input frequency	50 to 60 Hz	Energy-saving product	Yes
Power (Rated) (Nom)	20 W	Approval marks	RoHS compliance CE marking KEMA Keur certificate
Lamp current (nom.)	155 mA		
Starting time (nom.)	0.5 s		

Ecofit Ledtubes T8

Energy Consumption kWh/1000 h	20 kWh
Product Data	
Full product code	871869959532600
Order product name	Ecofit LEDtube 1500mm 20W 865 T8
EAN/UPC – product	8718699595326
Order code	59532600

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001338202
Net weight (piece)	0.270 kg



Dimensional drawing



TLED 5ft 220-240V 20-57W 2000lm 6500K


Product	D1	D2	A1	A2	A3
Ecofit LEDtube 1500mm 20W 865 T8	25.7 mm	28 mm	1500 mm	1507.1 mm	1514.2 mm

Photometric data



LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 20W G13 865 24D ND



LEDtube Ecofit 16W G13 865 24D ND



Ecofit Ledtubes T8

Lifetime




LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

Ecofit Ledtubes T8

