



CorePro LEDtube EM/ Mains T8

CorePro LEDtube 600mm 8W840

The CorePro LEDtube is an affordable LED solution suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Warnings and Safety

• –

Product data


General Information		Stroboscopic effect value (SVM)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	2	
Nominal lifetime	30,000 hour(s)	Photobiological safety according to EN 62471 RGO	
Switching Cycle	200,000		
Lighting Technology	LED	Operating and Electrical	
EU RoHS compliant	Yes	Line Frequency	50 to 60 Hz
		Input Frequency	50 to 60 Hz
		Power Consumption	8 W
		Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	220-240 V
		LED alternative to fluorescent lamp power	18 W
		Temperature	
		Ambient temperature range	-20 °C to 45 °C
		T-Case Maximum (Nom)	40 °C
Light Technical			
Color Code	840 [CCT of 4000K]		
Beam Angle (Nom)	240 degree(s)		
Luminous Flux	800 lm		
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	100.00 lm/W		
Color Consistency	<6		
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Flickering value (PstLM)	2		

CorePro LEDtube EM/Mains T8

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Glass
Product Length	600 mm
Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh



Product Data	
Order product name	CorePro LEDtube 600mm 8W840
Full product name	CorePro LEDtube 600mm 8W840
Full product code	871869671103300
Order code	71103300
Material Nr. (12NC)	929001338602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696711033
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696711040

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 8W840	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Photometric data




General uniform lighting - CorePro LEDtube 600mm 8W840

Spectral Power Distribution Colour - CorePro LEDtube 600mm 8W840


CorePro LEDtube EM/Mains T8

Photometric data




Light Distribution Diagram - CorePro LEDtube 600mm 8W840


Lifetime




Life Expectancy Diagram - CorePro LEDtube 600mm 8W840



Life Expectancy Diagram - CorePro LEDtube 600mm 8W840




Life Expectancy Diagram - CorePro LEDtube 600mm 8W840



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W840

CorePro LEDtube EM/Mains T8

Lifetime



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W840

