



CorePro LEDtube EM/ Mains T8

CorePro LEDtube 600mm 8W840

The CorePro LEDtube is an affordable LED solution suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	30000 h
Switching Cycle	200000X
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux (Nom)	800 lm
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	8 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Glass
Product Length	600 mm
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate


CorePro LEDtube EM/Mains T8

Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871869671103300
Order product name	CorePro LEDtube 600mm 8W840
EAN/UPC - Product	8718696711033
Order code	929001338602

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001338602
Net Weight (Piece)	0.120 kg

Warnings and Safety


Dimensional drawing




TLED 2ft 8-18W 800lm 4000K G13 Ess-Corep

Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 8W840	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Photometric data



LEDtube 600mm 8W G13 840 800lm



LEDtube 1500mm 20W G13 840 2200lm


CorePro LEDtube EM/Mains T8

Photometric data




LEDtube 1500mm 20W G13 840 2200lm

Lifetime



LEDtube 1500mm 20W G13 840 2200lm



LEDtube 1500mm 20W G13 840 2200lm

