



# MASTER LEDspot ExpertColor LV

## MAS LED MR16 ExpertColor 7.2-50W 940 60D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

### Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	40,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	60 degree(s)
Luminous Flux	480 lm
Luminous Intensity (Nom)	440 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	66.67 lm/W
Color Consistency	<3
Color rendering index (CRI)	97


LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	7.2 W
Lamp Current (Nom)	800 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	92 °C

# MASTER LEDspot ExpertColor LV

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	MAS LED MR16 ExpertColor 7.2-50W 940 60D


Full product name	MAS LED MR16 ExpertColor 7.2-50W 940 60D
Full product code	871869671954100
Order code	929001341608
Material Nr. (12NC)	929001341608
Local order code	MEC510LMR1660D
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696719541
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696719558

## Dimensional drawing



Product	D	C
MAS LED MR16 ExpertColor 7.2-50W 940 60D	50.5 mm	46 mm

## Photometric data




Spectral Power Distribution Colour - MAS LED MR16 ExpertColor 7.2-50W 940 60D

Accent Lighting Spots - MAS LED MR16 ExpertColor 7.2-50W 940 60D


# MASTER LEDspot ExpertColor LV

## Photometric data




Light Distribution Diagram - MAS LED MR16 ExpertColor 7.2-50W 940 60D

## Lifetime



Life Expectancy Diagram - MAS LED MR16 ExpertColor 7.2-50W 940 60D



Lumen Maintenance Diagram - MAS LED MR16 ExpertColor 7.2-50W 940 60D

