

PHILIPS

Eco passport

MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 24D MASTER LEDspot ExpertColor MV

MASTER LEDspot MV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates ambience with superior lighting that has a customised spectrum, high CRI and deep dimming features. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot LV and LEDspot Par lamps.



Our Eco passport



Energy

- Dimmable: Yes
- Energy efficiency label (EEL): A+
- Luminous efficacy (rated) (nom.): 73.64 lm/W
- Power (Rated) (Nom): 5.5 W



Circularity

- Nominal lifetime (nom.): 40000 h



Packaging

- SAP Weight Paper Unit (Case): 0.230 kg
- SAP Weight Paper Unit (Piece): 0.012 kg



Substances

- EU RoHS compliant: Yes
- RoHS mark: RoHS mark



Weight & Materials

- Net weight (piece): 0.040 kg

Energy efficiency ranking / External awards

