

PHILIPS

Eco passport

Master LED 5-50W GU10 940 36D Dim MASTER LEDspot MV Value

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimises maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere. For environments where the right atmosphere needs to be created (e.g. bars and restaurants), the “DimTone” feature could be useful. This is a LED feature that creates a warmer tone once light is dimmed down to lower intensities.



Our Eco passport



Energy

- Dimmable: Yes
- Energy efficiency label (EEL): A+
- Lamp Luminous Efficacy EM (Nom): 84.00 lm/W
- Power (Rated) (Nom): 5 W



Circularity

- Nominal lifetime (nom.): 25000 h



Packaging

- SAP Weight Paper Unit (Case): 0.230 kg
- SAP Weight Paper Unit (Piece): 0.012 kg



Substances

- EU RoHS compliant: No



Weight & Materials

- Net weight (piece): 0.038 kg

Energy efficiency ranking / External awards

