



# MASTER Plastic LEDbulbs

## MAS LED bulb DT 5.5-40WE27 927-922 A60FR

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	25,000 hour(s)
Switching Cycle	100,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	470 lm

Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5.5 W
Lamp Current (Nom)	31 mA

MASTER Plastic LEDbulbs

Wattage Equivalent	40 W
Starting Time (Nom)	0.3 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	70 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	A60 [A 60mm]


Approval and Application

Energy Consumption kWh/1000 h	6 kWh
-------------------------------	-------

Product Data


Order product name	MAS LED bulb DT 5.5-40WE27 927-922 A60FR
Full product name	MAS LED bulb DT 5.5-40WE27 927-922 A60FR
Full product code	871869670709800
Order code	929001351302
Material Nr. (12NC)	929001351302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707098
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707104

Dimensional drawing




Product	D	C
MAS LED bulb DT 5.5-40WE27 927-922 A60FR	60 mm	110 mm

Photometric data




General uniform lighting - MAS LED bulb DT 5.5-40WE27 927-922 A60FR



Spectral Power Distribution Colour - MAS LED bulb DT 5.5-40WE27 927-922 A60FR


# MASTER Plastic LEDbulbs

## Photometric data




Light Distribution Diagram - MAS LED bulb DT 5.5-40WE27 927-922 A60FR

## Lifetime



Life Expectancy Diagram - MAS LED bulb DT 5.5-40WE27 927-922 A60FR



Lumen Maintenance Diagram - MAS LED bulb DT 5.5-40WE27 927-922 A60FR

