



MASTER LEDbulb

MASTER LED bulb DT 5.5-40WE27 927-922 A60FR

The MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. They are particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimizes maintenance cost without any compromise on light quality. They can be used together with most leading-edge dimmers, enabling further efficiencies while helping to create the desired atmosphere.

Product data

General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Base	E27 [E27]		
EU RoHS compliant	Yes		
Nominal Lifetime (Nom)	25000 h		
Switching Cycle	100000X		
Technical Type	5.5-40W		
Light Technical		Operating and Electrical	
Color Code	922-927 [CCT of 2200K-2700K]	Input Frequency	50 to 60 Hz
Beam Angle (Nom)	200 °	Power (Rated) (Nom)	5.5 W
Initial lumen (Nom)	470 lm	Lamp Current (Nom)	31 mA
Color Designation	Warm White (WW)	Wattage Equivalent	40 W
Luminous Efficacy (rated) (Nom)	85.00 lm/W	Starting Time (Nom)	0.3 s
Color Consistency	<6	Warm Up Time to 60% Light (Nom)	0.5 s
Color Rendering Index (Nom)	90	Power Factor (Nom)	0.8
		Voltage (Nom)	220-240 V
		Temperature	
		T-Case Maximum (Nom)	70 °C

MASTER LEDbulb

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Frosted
-------------	---------

Approval and Application

Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	6 kWh


Product Data

Order product name	MASTER LED bulb DT 5.5-40WE27 927-922 A60FR
--------------------	---

EAN/UPC - Product	8718696707098
Order code	345421
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001351302
Net Weight (Piece)	0.060 kg

Warnings and Safety



Dimensional drawing



A60S230V6.5-40W470lm2.2-2.7KK E27D CRI90

Product	D	C
MASTER LED bulb DT 5.5-40WE27 927-922 A60FR	60 mm	110 mm

Photometric data




MASTER LEDbulb 40W E27 922-927 FR A60

MASTER LEDbulb 40W E27 922-927 FR A60


MASTER LEDbulb

Photometric data




MASTER LEDbulb 40W E27 922-927 FR A60

Lifetime



MASTER LEDspot PAR 50W E27 827 25D



MASTER LEDspot PAR 50W E27 827 25D

