

**PHILIPS**

Eco passport

## TrueForce LED HPI ND 200-145W E40 840 60D

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in High-bay applications. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus the initial investment is low. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour-rendering index enhance the lighting distribution while creating a comfortable, safe and high-productivity environment.



Our Eco passport



### Energy

- Dimmable: No
- Energy efficiency label (EEL): A+
- Luminous efficacy (rated) (nom.): 137.00 lm/W
- Power (Rated) (Nom): 145 W



### Circularity

- Nominal lifetime (nom.): 50000 h



### Packaging

- SAP Weight Paper Unit (Case): 1.037 kg
- SAP Weight Paper Unit (Piece): 0.230 kg
- SAP Weight Plastic Unit (Case): 0.469 kg
- SAP Weight Plastic Unit (Piece): 0.235 kg



### Substances

- EU RoHS compliant: Yes
- RoHS mark: RoHS mark



### Weight & Materials

- Net weight (piece): 1.300 kg

Energy efficiency ranking / External awards

