



CorePro LEDspot MV

CorePro LEDspot 4-35W GU10 830 36D DIM

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap base	GU10 [GU10]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	4-35W
Light Technical	
Colour code	830 [CCT of 3,000 K]
Beam Angle (Nom)	36 °
Luminous flux (nom.)	260 lm
Luminous intensity (nom.)	540 cd
Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	65.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	260 lm
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W


Lamp current (nom.)	19 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	65 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
Product Data	
Full product code	871869672135300
Order product name	CorePro LEDspot 4-35W GU10 830 36D DIM
EAN/UPC – product	8718696721353
Order code	72135300

CorePro LEDspot MV

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001363902

Net weight (piece)	0.038 kg
--------------------	----------


Dimensional drawing




GU10 230V 4-35W 260lm 36D 3000K GU10 D

Product	D	C
CorePro LEDspot 4-35W GU10 830 36D DIM	50 mm	54 mm


Photometric data



LEDspot,PAR38 11W 900lm 3000K





Classic LEDspotMV 35W GU10 830 36D



CorePro LEDspotMV 35W GU10 830 36D CLA

CorePro LEDspot MV

Lifetime



CLA LEDspotMV 50W GU10 827 36D ND

CLA LEDspotMV 50W GU10 827 36D ND

