

PHILIPS

Eco passport

Master LED PAR30L 40W 15D 840

MASTER LEDspot PAR High Lumen

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.



Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

Energy

- Dimmable: No
- Energy efficiency label (EEL): A+
- Luminous efficacy (rated) (nom.): 105.00 lm/W
- Power (Rated) (Nom): 40 W

Circularity

- Nominal lifetime (nom.): 25000 h

Packaging

- SAP Weight Paper Unit (Case): 0.717 kg
- SAP Weight Paper Unit (Piece): 0.074 kg

Substances

- EU RoHS compliant: Yes

Weight & Materials

- Net weight (piece): 0.410 kg

Energy efficiency ranking / External awards



Further reading at:
<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2020 Signify Holding. All rights reserved.