



# MASTER LEDspot PAR High Lumen

## Master LED PAR30L 40W 15D 857

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

### Product data

General Information	
Cap base	E27 [ E27]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	40-70W
Light Technical	
Colour Code	857 [ CCT of 5,700 K]
Technical Beam Angle (Nom)	15 °
Lamp Luminous Flux 25°C EL (Nom)	4200 lm
Luminous intensity (nom.)	42000 cd
Colour Designation	Daylight
Colour Temperature, horizontal (Nom)	5700 K
Lamp Luminous Efficacy EM (Nom)	105.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	82
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz


Power (Rated) (Nom)	40 W
Lamp current (nom.)	196 mA
Wattage equivalent	70 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	90 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	40 kWh

# MASTER LEDspot PAR High Lumen

Product Data	
Full product code	871869675937000
Order product name	Master LED PAR30L 40W 15D 857
EAN/UPC – product	8718696759370
Order code	929001374608
Numerator – quantity per pack	1

Numerator – packs per outer box	6
Material no. (12NC)	929001374608
Net weight (piece)	0.410 kg


## Dimensional drawing




PAR30L 35-35W 4000lm 15D 6000K E27 ND

Product	D	C
Master LED PAR30L 40W 15D 857	95.5 mm	129 mm

## Photometric data




LEDspot E27 PAR30L 35W 6000K




LEDspot E27 PAR30L 35W 6000K

## Lifetime



LEDspot E27 PAR30L 35W 4000K



LEDspot E27 PAR30L 35W 4000K

## MASTER LEDspot PAR High Lumen

