

PHILIPS

Eco passport

Master LED PAR30L 40W 30D 840

MASTER LEDspot PAR



With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Our Eco passport



Energy

- Dimmable: No
- Energy efficiency label (EEL): A+
- Lamp Luminous Efficacy EM (Nom): 115.00 lm/W
- Power (Rated) (Nom): 40 W



Circularity

- Nominal lifetime (nom.): 25000 h



Packaging

- SAP Weight Paper Unit (Case): 0.717 kg
- SAP Weight Paper Unit (Piece): 0.074 kg



Substances

- EU RoHS compliant: No



Weight & Materials

- Net weight (piece): 0.410 kg

Energy efficiency ranking / External awards

