

Master LED PAR30L 40W 30D 840 MASTER LEDspot PAR High Lumen

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



- Dimmable: No
- Luminous Efficacy (rated) (Nom): 115.00 lm/W
- Power (Rated) (Nom): 40 W

Circularity

• Nominal Lifetime (Nom): 25000 h



- SAP Weight Paper Unit (Case): 0.717 kg
- SAP Weight Paper Unit (Piece): 0.074 kg



• EU REACH restrictions compliant: Yes

• EU RoHS compliant: Yes



Weight & Materials

• Net Weight (Piece): 0.410 kg