



MASTER LEDtube EM/ Mains T8

MAS LEDtube STD 1200mm 14W865 T8 I W

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime ensure this tube masters every demanding application.

Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.

Product data


General Information		Color Consistency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Color rendering index (CRI)	<6
Nominal lifetime	50,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)	70 %
Switching Cycle	200,000	Operating and Electrical	
Lighting Technology	LED	Line Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Input Frequency	50 to 60 Hz
Light Technical		Power Consumption	14 W
Color Code	865 [CCT of 6500K]	Lamp Current (Max)	170 mA
Beam Angle (Nom)	160 degree(s)	Lamp Current (Min)	50 mA
Luminous Flux	2,100 lm	Starting Time (Nom)	0.5 s
Color Designation	Cool Daylight	Warm-up time to 60% light	0.5 s
Correlated Color Temperature (Nom)	6500 K	Power Factor (Fraction)	0.92
Luminous Efficacy (rated) (Nom)	150.00 lm/W		

MASTER LEDtube EM/Mains T8

Voltage (Nom)	100-277 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Product Length	1,200 mm
Bulb Shape	Tube, double-ended
Approval and Application	
Energy Saving Product	Yes



Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	14 kWh
Product Data	
Order product name	MAS LEDtube STD 1200mm 14W865 T8 I W
Full product name	MAS LEDtube STD 1200mm 14W865 T8 I W
Order code	929001375542
Material Nr. (12NC)	929001375542
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677554378
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677554373

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube STD 1200mm 14W865 T8 I W	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Photometric data




General uniform lighting - MAS LEDtube STD 1200mm 14W865 T8 I W

Spectral Power Distribution Colour - MAS LEDtube STD 1200mm 14W865 T8 I W


MASTER LEDtube EM/Mains T8

Photometric data




Light Distribution Diagram - MAS LEDtube STD 1200mm 14W865 T8 I W


Lifetime




Life Expectancy Diagram - MAS LEDtube STD 1200mm 14W865 T8 I W



Life Expectancy Diagram - MAS LEDtube STD 1200mm 14W865 T8 I W




Lumen Maintenance Diagram - MAS LEDtube STD 1200mm 14W865 T8 I W



Lumen Maintenance Diagram - MAS LEDtube STD 1200mm 14W865 T8 I W

MASTER LEDtube EM/Mains T8

Lifetime



Life Expectancy Diagram - MAS LEDtube STD 1200mm 14W865 T8 I W

