



MASTER LEDtube EM/ Mains T8

MAS LEDtube 1200mm UE 14.5W 840 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Warnings and Safety

• –

Product data


General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	G13 ROT (Rotating) [Medium Bi-Pin Fluorescent]	Operating and Electrical	
Nominal lifetime	70,000 hour(s)	Line Frequency	50 to 60 Hz
Switching Cycle	200,000	Input Frequency	50 to 60 Hz
Lighting Technology	LED	Power Consumption	14.5 W
EU RoHS compliant	Yes	Lamp Current (Max)	74 mA
Light Technical		Lamp Current (Min)	56 mA
Color Code	840 [CCT of 4000K]	Starting Time (Nom)	0.5 s
Beam Angle (Nom)	160 degree(s)	Warm-up time to 60% light	0.5 s
Luminous Flux	2,500 lm	Power Factor (Fraction)	0.9
Color Designation	Cool White (CW)	Voltage (Nom)	220-240 V
Correlated Color Temperature (Nom)	4000 K	Temperature	
Luminous Efficacy (rated) (Nom)	172.00 lm/W	Ambient temperature range	-20 °C to 35 °C
Color Consistency	<6	T-Case Maximum (Nom)	55 °C
Color rendering index (CRI)	83		

MASTER LEDtube EM/Mains T8

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Plastic
Product Length	1,200 mm
Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	15 kWh



Product Data	
Order product name	MAS LEDtube 1200mm UE 14.5W 840 T8
Full product name	MAS LEDtube 1200mm UE 14.5W 840 T8
Full product code	871869673150500
Order code	929001376802
Material Nr. (12NC)	929001376802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696731505
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696731512

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm UE 14.5W 840 T8	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Photometric data




General uniform lighting - MAS LEDtube 1200mm UE 14.5W 840 T8

Spectral Power Distribution Colour - MAS LEDtube 1200mm UE 14.5W 840 T8


MASTER LEDtube EM/Mains T8

Photometric data




Light Distribution Diagram - MAS LEDtube 1200mm UE 14.5W 840 T8


Lifetime




Lumen Maintenance Diagram - MAS LEDtube 1200mm UE 14.5W 840 T8



Life Expectancy Diagram - MAS LEDtube 1200mm UE 14.5W 840 T8




Life Expectancy Diagram - MAS LEDtube 1200mm UE 14.5W 840 T8



Life Expectancy Diagram - MAS LEDtube 1200mm UE 14.5W 840 T8

MASTER LEDtube EM/Mains T8

Lifetime



Lumen Maintenance Diagram - MAS LEDtube 1200mm UE 14.5W 840 T8

