

Essential LEDtube

CorePro LEDtube 1200mm 16W840 G5 I APR

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.


产品数据

一般信息	
底盖	G5
标称使用寿命	30,000 小时
切换循环	50,000
照明技术	LED
符合欧盟 RoHS 规范	是
灯技术	
颜色代码	840 [CCT of 4000K]
光束角度 (标称)	200 °
光通量	2,100 lm
颜色名称	冷白色 (CW)
相关色温 (标称)	4000 K
光效 (额定) (标称)	131.00 lm/W
颜色一致性	<6
显色指数 (CRI)	80
标称使用寿命结束时灯的光通维持率 (标称)	70 %
操作和电气	
线频率	50 to 60 Hz
输入频率	50 至 60 Hz
功耗	16 W
灯具电流 (最大)	178 mA


灯具电流 (最小)	77 mA
启动时间 (标称)	0.5 s
60% 灯光下的预热时间	0.5 s
功率系数 (小数)	0.92
电压 (标称)	100-240 V
温度	
环境温度范围	-20 °C 至 45 °C
最大外壳温度 (标称)	70 °C
控制和调光	
可调光	否
机械和外壳	
产品长度	1,200 mm
灯泡外形	T5 [16 毫米 (T5)]
审批和申请	
节能产品	是
批准标志	CE 标志 遵从 RoHS KEMA Keur 证书
能耗 kWh/1000 h	16 kWh

产品数据	
订单产品名称	CorePro LEDtube 1200mm 16W840 G5 I APR
完整的产品名称	CorePro LEDtube 1200mm 16W840 G5 I APR
完整产品代码	871869673204500
订购代码	929001381008
材料编号 (12NC)	929001381008


二维绘图



光度数据




General uniform lighting - CorePro LEDtube 1200mm 16W840 G5 I APR



Light Distribution Diagram - CorePro LEDtube 1200mm 16W840 G5 I APR



计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718696732045
计算器 - 每个外包装箱中的包数	20
EAN/UPC - 案例	8718696732052

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 16W840 G5 I APR	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm




Spectral Power Distribution Colour - CorePro LEDtube 1200mm 16W840 G5 I APR


寿命




Life Expectancy Diagram - CorePro LEDtube 1200mm 16W840 G5 I APR



Life Expectancy Diagram - CorePro LEDtube 1200mm 16W840 G5 I APR



Life Expectancy Diagram - CorePro LEDtube 1200mm 16W840 G5 I APR



Lumen Maintenance Diagram - CorePro LEDtube 1200mm 16W840 G5 I APR

Lumen Maintenance Diagram - CorePro LEDtube 1200mm 16W840 G5 I APR

