



MASTER LEDspot ExpertColor LV

MASTER LED ExpertColor LED ExpertColor 7.5-43W MR16 927 24D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV lamps.

Product data

General Information	
Cap base	GU5.3 [GU5.3]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	40000 h
Switching cycle	50000X
Technical type	7.5-43W
Light Technical	
Colour code	927
Beam Angle (Nom)	24°
Luminous flux (nom.)	485 lm
Luminous intensity (nom.)	2400 cd
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	64.67 lm/W
Colour consistency	<3

Color rendering index (nom.)	92
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	485 lm
Operating and Electrical	
Power (Rated) (Nom)	7.5 W
Lamp current (nom.)	880 mA
Wattage equivalent	43 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case maximum (nom.)	93 °C

MASTER LEDspot ExpertColor LV

Controls and Dimming

Dimmable Yes

Approval and Application

Energy efficiency label (EEL) A

Suitable for accent lighting Yes

Energy Consumption kWh/1000 h 9 kWh

Product Data

Full product code 871869673538100

Order product name MASTER LED ExpertColor LED
ExpertColor 7.5-43W MR16 927 24D

EAN/UPC – product 8718696735381

Order code 73538100


Numerator – quantity per pack 1

Numerator – packs per outer box 10

Material no. (12NC) 929001386002

Net weight (piece) 0.034 kg


Dimensional drawing




MR16 12V 8-43W 550lm 24D 2700K GU5.3 D

Product	D	C
MASTER LED ExpertColor LED ExpertColor 7.5-43W MR16 927 24D	50.5 mm	46 mm

Photometric data



Copyright Philips Lighting B.V. All rights reserved.




MAS LEDspotLV 43W GU5-3 927 24D MR16

MAS LEDspotLV 43W GU5-3 927 24D MR16


MASTER LEDspot ExpertColor LV

Photometric data



MAS LEDspotLV 43W GU5-3 927 24D MR16

Lifetime



MAS LEDspotLV 43W GU5-3 927 24D MR16



MAS LEDspotLV 43W GU5-3 927 24D MR16

