



MASTER LEDtube InstantFit HF T5

Master LEDtube HF 1200mm HE 16.5W 830 T5

Philips MASTER LEDtube InstantFit T5 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescents. The Philips MASTER LEDtube InstantFit T5 is the ideal solution for customers who have higher light output requirements and want to maximise value over the lifetime. The full energy savings & longer lifetime result in attractive payback times and TCO benefits.

Product data

General Information		Warm-up time to 60% light (nom.)		0.5 s
Cap base	G5 [G5]	Power factor (nom.)	0.9	
Nominal lifetime (nom.)	50000 h	Voltage (Nom)	90-130 V	
Switching cycle	50000X	Temperature		
Light Technical		T ambient (max.)	45 °C	
Colour Code	830 [CCT of 3,000 K]	T ambient (min.)	-20 °C	
Lamp Luminous Flux 25°C EL (Nom)	2300 lm	T storage (max.)	65 °C	
Colour Temperature, horizontal (Nom)	3000 K	T storage (min.)	-40 °C	
Colour consistency	<6	T-Case maximum (nom.)	65 °C	
Colour Rendering Index,horiz (Nom)	83	Controls and Dimming		
LLMF at end of nominal lifetime (nom.)	70 %	Dimmable	No	
Operating and Electrical		Mechanical and Housing		
Input frequency	35000-70000 Hz	Bulb material	Glass	
Power (Rated) (Nom)	16.5 W	Product length	1200 mm	
Lamp current (max.)	350 mA			
Lamp current (min.)	150 mA			
Starting time (nom.)	0.5 s			

MASTER LEDtube InstantFit HF T5

Approval and Application


Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	20 kWh

Product Data

Full product code	871869674329400
-------------------	-----------------

Order product name	Master LEDtube HF 1200mm HE 16.5W 830 T5
EAN/UPC – product	8718696743294
Order code	929001391002
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001391002
Net weight (piece)	0.159 kg


Dimensional drawing



TLED 1200mm 230V14W-28W 2100lm 160D 300


Product	D1	D2	A1	A2	A3
Master LEDtube HF 1200mm HE 16.5W 830 T5	15.5 mm	18.8 mm	1149 mm	1156.1 mm	1163.2 mm

Photometric data



General Information 14 Recycling 14 Page 14



LEDtube 1200mm 16-5W G5 830 2300lm



LEDtube 600mm 8W G5 830 1000lm



MASTER LEDtube InstantFit HF T5

Lifetime




LEDtube 600mm 8W G5 830 1000lm

LEDtube 600mm 8W G5 830 1000lm



LEDtube 600mm 8W G5 830 1000lm

LEDtube 600mm 8W G5 830 1000lm



LEDtube 600mm 8W G5 830 1000lm

MASTER LEDtube InstantFit HF T5

