

PHILIPS

Eco passport

Master LEDtube HF 1200mm HE 16.5W 865 T5 MASTER LEDtube InstantFit HF T5

Philips MASTER LEDtube InstantFit T5 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescents. The Philips MASTER LEDtube InstantFit T5 is the ideal solution for customers who have higher light output requirements and want to maximise value over the lifetime. The full energy savings & longer lifetime result in attractive payback times and TCO benefits.



Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- Dimmable: No
- Energy efficiency label (EEL): A++
- Power (Rated) (Nom): 16.5 W



Circularity

- Nominal lifetime (nom.): 50000 h



Packaging

- SAP Weight Paper Unit (Case): 1.071 kg
- SAP Weight Paper Unit (Piece): 0.032 kg



Substances

- EU RoHS compliant: Yes



Weight & Materials

- Net weight (piece): 0.159 kg

Energy efficiency ranking / External awards



Further reading at:
<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2020 Signify Holding. All rights reserved.