



LED Urban TrueForce Lamps

55ED28/LED/727/ND 120-277V G2 4/1

Philips TrueForce LED high lumen post top lamp makes it easy to upgrade to long lasting, energy saving LED technology without sacrificing your site's unique outdoor character. Philips TrueForce is a direct replacement option which ensures a perfect fit with existing modern and traditional luminaires. We claim true replacement when comparing flux. This post top lamps can be used in enclosed fixtures.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	55-150W
Light Technical	
Color Code	727 [CCT of 2700K]
Beam Angle (Nom)	360 °
Luminous Flux (Nom)	7500 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	133.33 lm/W
Color Consistency	ANSI 2700K
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Rated) (Nom)	55 W
Lamp Current (Nom)	460 mA
Wattage Equivalent	150 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Certifications	DLC Standard

LED Urban TrueForce Lamps


DesignLights Consortium Qualified Product List -

Product Data

Order product name	55ED28/LED/727/ND 120-277V G2 4/1
EAN/UPC - Product	046677473655
Order code	473652

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001397004
Net Weight (Piece)	0.900 kg



Dimensional drawing



HIB NAM Post top 8000lm 2700K G2


Product	D	C
55ED28/LED/727/ND 120-277V G2 4/1	105 mm	204 mm

Photometric data



HIB NAM Trueforce 55W E39 Clear 727 36D ND


HIB NAM Trueforce 55W E39 Clear 727 36D ND




HIB NAM Trueforce 26W-38W-55W E26-E39 Clear 727 36D ND

LED Urban TrueForce Lamps

Lifetime



HIB NAM Trueforce 26W E26 Clear 730 36D ND



HIB NAM Trueforce 26W E26 Clear 730 36D ND

