

PHILIPS

Eco passport

13T8 LED/48-3000 IF DIM 1PK 10/1

MasterClass LEDtube InstantFit T8

The Masterclass LED Type A - Ballast Driven (Plug and Play) InstantFit TLED is a great LED solutionsuitable for replacing T8 fluorescent lamps, using an existing ballast. Specific lamps can also be used on Philips Xitanium driver for Type C applications.



Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- **Dimmable:** Yes
- **Power (Rated) (Nom):** 13 W



Circularity

- **Nominal Lifetime (Nom):** 70000 h



Packaging

- **SAP Weight Paper Unit (Case):** 0.519 kg



Substances

- **BFR policy compliant:** No
- **EU REACH restrictions compliant:** Yes
- **EU RoHS compliant:** Yes
- **EU RoHS phthalates compliant:** Yes
- **PVC policy compliant:** Yes
- **RoHS mark:** RoHS mark



Weight & Materials

- **Net Weight (Piece):** 0.230 kg

Further reading at:
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2019 Signify Holding. All rights reserved.