

# T8

## 13T8 LED/48-5000 IF DIM 1PK 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	70000 h
Switching Cycle	50000X
Light Technical	
Color Code	850 [ CCT of 5000K]
Luminous Flux (Nom)	2100 lm
Correlated Color Temperature (Nom)	5000 K
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	20000-120000 Hz
Power (Nom)	13 W
Lamp Current (Max)	400 mA
Lamp Current (Min)	130 mA
Starting Time (Nom)	0.5 s


Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277V; 347 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Product Length	1200 mm
Approval and Application	
Energy Saving Product	Yes

# T8

Approval Marks	UL certificate RoHS compliance DLC compliance
<b>Product Data</b>	
Order product name	13T8 LED/48-5000 IF DIM 1PK 10/1
EAN/UPC - Product	046677473952
Order code	929001397904

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001397904
Net Weight (Piece)	0.230 kg


## Dimensional drawing




TLED IF MasterClass 4ft 2100lm 5000K

Product	D1	D2	A1	A2	A3
13T8 LED/48-5000 IF DIM 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm


## Photometric data



LEDtube 15W G13 850 160D IF 6U EasySmart





LEDtube 13W G13 850 IF DIM





LEDtube 13W G13 2100lm

Lifetime




LEDtube 13W G13 2100lm

LEDtube 13W G13 2100lm



LEDtube 13W G13 2100lm

LEDtube 13W G13 2100lm



LEDtube 13W G13 2100lm

