

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

TForce Core HB 200-160W E40 840 WB GM

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in Highbay application. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus they come for a low initial investment. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour rendering index enhance the lighting distribution while creating a comfortable, safe and high productivity environment.

Warnings and Safety

• EM version requires an EM ballast to operate. Please refer to the installation guide or consult a Philips Lighting representative.

Product data

General Information	
Cap-Base	E40 [E40]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	130 degree(s)

Luminous Flux	20,000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	125.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Input Frequency	50 to 60 Hz
Power Consumption	160 W
Lamp Current (Nom)	1,900 mA
Starting Time (Nom)	0.7 s
Warm-up time to 60% light	0.7 s
Power Factor (Fraction)	0.9
Voltage (Nom)	110-277 V

Temperature	
T-Case Maximum (Nom)	100 °C


Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T50 [T 50mm]

Approval and Application	
Energy Consumption kWh/1000 h	- kWh


Product Data	
Order product name	TForce Core HB 200-160W E40 840 WB GM
Full product name	TForce Core HB 200-160W E40 840 WB GM
Full product code	871869676934800
Order code	929001812508
Material Nr. (12NC)	929001812508
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696769348
Numerator - Packs per outer box	2
EAN/UPC - Case	8718696769355

Dimensional drawing




Product	D	C
TForce Core HB 200-160W E40 840 WB GM	211 mm	263 mm

Photometric data




General uniform lighting - TForce Core HB 200-160W E40 840 WB GM



Light Distribution Diagram - TForce Core HB 200-160W E40 840 WB GM


TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data




Spectral Power Distribution Colour - TForce Core HB 200-160W E40 840 WB GM


Lifetime



Life Expectancy Diagram - TForce Core HB 200-160W E40 840 WB GM



Life Expectancy Diagram - TForce Core HB 200-160W E40 840 WB GM



Lumen Maintenance Diagram - TForce Core HB 200-160W E40 840 WB GM

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com
2023, April 29 - data subject to change