



MasterConnect LEDtube EM/Mains T8

MASTERConnect LEDtube IA 1200mm UO 16.5W830 T8

Philips MasterConnect LEDtube EM/Mains T8 means easy upgrade to a connected lighting system. Its 2.4GHz mesh networking technology enables wireless integration with a variety of control devices, such as sensor and switch. The result? Even more energy saving and enhanced flexibility in your space. Through dimming, occupancy sensing and/or daylight harvesting, lamps deliver 50% or more energy saving thanks to MasterConnect technology.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Connectivity	Interact Ready
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	2,300 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	139.39 lm/W
Color Consistency	<6
Color rendering index (CRI)	83


LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	16.5 W
Lamp Current (Max)	76 mA
Lamp Current (Min)	69 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	45 °C

MasterConnect LEDtube EM/Mains T8

Controls and Dimming	
Dimmable	Wireless Dim
Mechanical and Housing	
Product Length	1,200 mm
Bulb Shape	Tube, double-ended
Approval and Application	
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	17 kWh



Product Data	
Order product name	MAScon LEDtube IA 1200mm UO 16.5W830 T8
Full product name	MASTERConnect LEDtube IA 1200mm UO 16.5W830 T8
Full product code	871869677342000
Order code	77342000
Material Nr. (12NC)	929001813702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696773420
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696773437

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAScon LEDtube IA 1200mm UO 16.5W830 T8	25.7 mm	28 mm	1,199.4 mm	1,205.3 mm	1,212.4 mm

Photometric data




General uniform lighting - MAScon LEDtube IA 1200mm UO 16.5W830 T8

Light Distribution Diagram - MAScon LEDtube IA 1200mm UO 16.5W830 T8


MasterConnect LEDtube EM/Mains T8

Photometric data




Spectral Power Distribution Colour - MAScon LEDtube IA 1200mm UO 16.5W830 T8


Lifetime




Life Expectancy Diagram - MAScon LEDtube IA 1200mm UO 16.5W830 T8



Life Expectancy Diagram - MAScon LEDtube IA 1200mm UO 16.5W830 T8



Lumen Maintenance Diagram - MAScon LEDtube IA 1200mm UO 16.5W830 T8



Lumen Maintenance Diagram - MAScon LEDtube IA 1200mm UO 16.5W830 T8

MasterConnect LEDtube EM/Mains T8

Lifetime



Life Expectancy Diagram - MAScon LEDtube IA 1200mm UO 16.5W830 T8

