



Classic filament LEDbulbs

CLA LEDBulb ND 4-40W A60 E27 840 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	4-40W
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux (Nom)	540 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	135.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	4 W

Lamp Current (Nom)	38 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	4 kWh


Classic filament LEDbulbs

Product Data

Full product code	871869676698900
Order product name	CLA LEDBulb ND 4-40W A60 E27 840 CL
EAN/UPC - Product	8718696766989
Order code	929001814902
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001814902
Net Weight (Piece)	0.030 kg


Dimensional drawing




Bulb A60 230V 4-40W 470lm 4000K E27 ND

Product	D	C
CLA LEDBulb ND 4-40W A60 E27 840 CL	60 mm	106 mm


Photometric data



CLA LEDbulb 40W E27 840 CL A60




CLA LEDbulb 60W E27 840 CL A60



CLA LEDbulb 40W B22 827 CL A60 ND

Classic filament LEDbulbs

Lifetime



LEDbulb 60W E14 827 FR B38

LEDbulb 60W E14 827 FR B38

