



LED Urban TrueForce Lamps

38ED28/LED/730/ND 120-277V G2 CT 4/1

Philips TrueForce LED high lumen post top lamp makes it easy to upgrade to long lasting, energy saving LED technology without sacrificing your site's unique outdoor character. Philips TrueForce is a direct replacement option which ensures a perfect fit with existing modern and traditional luminaires. We claim true replacement when comparing flux. This post top lamps can be used in enclosed fixtures.

Product data

General Information	
Base	E39 [Single Contact Mogul Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	38-100W
Light Technical	
Color Code	730 [CCT of 3000K]
Beam Angle (Nom)	360 °
Initial lumen (Nom)	5000 lm
Luminous Flux (Rated) (Nom)	5000 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	60.00 lm/W
Color Consistency	ANSI 3000K
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	38 W
Lamp Current (Nom)	320 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.6 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

LED Urban TrueForce Lamps

Approval and Application


Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-

Product Data

Order product name	38ED28/LED/730/ND 120-277V G2 CT 4/1
--------------------	--------------------------------------

EAN/UPC - Product	046677476045
Order code	476044
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001818404
Net Weight (Piece)	0.880 kg


Dimensional drawing




HIB NAM Post top CT 5000lm 3000K

Product	D	C
38ED28/LED/730/ND 120-277V G2 CT 4/1	105 mm	245 mm


Photometric data



High Intensity 40W E39 ED-28 Clear 3000K





HIB NAM Trueforce 38W E39 Clear 730 36D ND



HIB NAM Trueforce 38W E39 Clear 727 36D ND

LED Urban TrueForce Lamps

Lifetime



HIB NAM Trueforce 38W E39 Clear 727 36D ND

HIB NAM Trueforce 38W E39 Clear 727 36D ND

