



Indoor Accessories

OCC-DL SENSOR IA CM IP42 WH

Indoor lighting control accessories cover all the user interfaces, sensors, cables, dimmers and other accessories that can be used with our control systems or stand-alone with our lighting systems. The performance and capabilities of the products vary according to the system they are connected to.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Rated Lifetime (Hours)	50,000 hour(s)
Connectivity	Interact Ready
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Power Consumption	1 W
Voltage (Nom)	3.7 V
Temperature	
Ambient temperature range	-5 °C to 45 °C

Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking UL certificate
Product Data	
Order product name	OCC-DL SENSOR IA CM IP42 WH
Full product name	OCC-DL SENSOR IA CM IP42 WH
Full product code	694793914939100
Order code	929001819110
Material Nr. (12NC)	929001819110
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6947939149391
Numerator - Packs per outer box	10
EAN/UPC - Case	6947939149407