



PL-C/T

12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data

General Information		Lamp Current (Min)	
Cap-Base	GX24q		150 mA
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Main Application	Industrial	Warm Up Time to 60% Light (Nom)	0.5 s
Nominal Lifetime (Nom)	50000 h	Power Factor (Nom)	0.9
Switching Cycle	50000X	Voltage (Nom)	25-55 V
Technical Type	12-32W	Temperature	
Light Technical		T-Ambient (Max)	45 °C
Color Code	827 [CCT of 2700K]	T-Ambient (Min)	-20 °C
Luminous Flux (Nom)	1350 lm	T-Storage (Max)	65 °C
Luminous Flux (Rated) (Nom)	1350 lm	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	2700 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	112.00 lm/W	Dimmable	Yes
Color Consistency	<6	Mechanical and Housing	
Color Rendering Index (Nom)	82	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Plastic
Operating and Electrical		Product Length	100 mm
Input Frequency	20000-100000 Hz	Approval and Application	
Power (Nom)	12 W	Energy Saving Product	Yes
Lamp Current (Max)	500 mA		

PL-C/T


Approval Marks	RoHS compliance UL certificate KEMA Keur certificate DLC compliance
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-

Product Data

Order product name	12PLC/T LED/32V/827/1F/4P/DIM 1PK 10/1
---------------------------	---

EAN/UPC - Product	046677476106
Order code	929001820104
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001820104
Net Weight (Piece)	0.082 kg


Dimensional drawing




PLED 120V 12-32W 1350lm 2700K G24/Gx24

Product	D1	D2	A1	A2	A3
12PLC/T LED/32V/827/1F/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm

Photometric data




LEDtube PLC/T 12W G24Q 827 32V DIM




LEDtube PLC/T 12W G24Q 827 32H-32V DIM

Photometric data




LEDtube PLC/T 12W G24Q 827 32V DIM


Lifetime




LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM



LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM




LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM



LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM

PL-C/T

Lifetime



LEDtube PLC/T 12W G24Q 827-840 32V DIM

