



# A-Shape LED

## 9A19/LED/927/P/E26/ND 4/4FB T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	10,950 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	927
Beam Angle (Nom)	250 degree(s)
Luminous Flux	800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	88.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	9 W
Lamp Current (Nom)	85 mA
Wattage Equivalent	60 W

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	167 °F

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19 [A 19mm]

Approval and Application	
Energy Consumption kWh/1000 h	- kWh


Product Data	
Order product name	9A19/LED/927/P/E26/ND 4/4FB T20
Full product name	9A19/LED/927/P/E26/ND 4/4FB T20
Order code	531798
Material Nr. (12NC)	929001825723

# A-Shape LED

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677531799
Numerator - Packs per outer box	4



EAN/UPC - Case	50046677531794
----------------	----------------

## Dimensional drawing




Product	D	C
9A19/LED/927/P/E26/ND 4/4FB T20	2-7/16 inch	4-1/4 inch

## Photometric data



Spectral Power Distribution Colour - 9A19/LED/927/P/E26/ND 4/4FB T20



General uniform lighting - 9A19/LED/927/P/E26/ND 4/4FB T20



Light Distribution Diagram - 9A19/LED/927/P/E26/ND 4/4FB T20

# A-Shape LED

## Lifetime



Life Expectancy Diagram - 9A19/LED/927/P/E26/ND 4/4FB T20

Lumen Maintenance Diagram - 9A19/LED/927/P/E26/ND 4/4FB T20

